

SPECIFICATION

Hydrogen Peroxide
for Isolator

| REQUIREMENT | SPECIFICATION |
|---------------------------|------------------------|
| Appearance | Colorless clear liquid |
| Residue after evaporation | max.10ppm |
| Chloride (Cl) | max.1ppm |
| Phosphate (PO4) | max.1ppm |
| Sulfate (SO4) | max.1ppm |
| Sodium (Na) | max.50ppb |
| Potassium (K) | max.50ppb |
| Copper (Cu) | max.10ppb |
| Aluminium (Al) | max.500ppb |
| Tin (Sn) | measured value |
| Lead (Pb) | max.100ppb |
| Arsenic (As) | max.5ppb |
| Iron (Fe) | max.50ppb |
| Total nitrogen (N) | max.2ppm |
| Isolater test | to pass test |
| Assay | 34.0~36.0% |