

## SPECIFICATION

Liquid Paraffin [Density (20°C) 0.825~0.850g/mL]

Wako Special Grade

REQUIREMENT	SPECIFICATION
Appearance	Colorless clear liquid
Viscosity (37.8°C)	11.7~14.4mm <sup>2</sup> /s
Density (20°C)	0.825~0.850g/mL
Acidity and alkalinity	to pass test
Chloride (Cl)	max.0.001%
Sulfate (SO <sub>4</sub> )	max.0.002%
Sulfide	to pass test
Polycyclic aromatic hydrocarbons	to pass test
Solid paraffin	to pass test
Substances darkened by sulfuric acid	to pass test
Substances reducing permanganate	to pass test