

SPECIFICATION

2-(2-Butoxyethoxy)ethanol

for RoHS

REQUIREMENT	SPECIFICATION
Appearance	Colorless clear liquid
Solubility in water	to pass test
Density (20°C)	0.950~0.956g/ml
Water	max.0.2%
Assay (capillary GC)	min.98.0%
Cadmium (Cd) (RoHS)	max.10ppm
Mercury (Hg) (RoHS)	max.10ppm
Lead (Pb) (RoHS)	max.100ppm
Chromium (Cr) (RoHS)	max.10ppm
Brominated flame retardants (as Br) (RoHS)	max.10ppm