

SPECIFICATION

Phosphoric Acid

for RoHS

REQUIREMENT	SPECIFICATION
Appearance	Colorless clear liquid
Assay (H ₃ PO ₄)	min.85.0%(mass/mass)
Solubility in ethanol	to pass test
Volatile acids (as CH ₃ COOH)	max.0.001%(mass/mass)
Chloride (Cl)	max.2ppm(mass/mass)
Nitrate	to pass test
Sulfate (SO ₄)	max.0.002%(mass/mass)
Sodium (Na)	max.0.01%(mass/mass)
Potassium (K)	max.0.005%(mass/mass)
Copper (Cu)	max.5ppm(mass/mass)
Zinc (Zn)	max.5ppm(mass/mass)
Cadmium (Cd)	max.5ppm(mass/mass)
Lead (Pb)	max.5ppm(mass/mass)
Arsenic (As)	max.0.5ppm(mass/mass)
Manganese (Mn)	max.5ppm(mass/mass)
Iron (Fe)	max.5ppm(mass/mass)
Nickel (Ni)	max.5ppm(mass/mass)
Substances reducing permanganate (as H ₃ PO ₃)	max.0.005%(mass/mass)
Cadmium (Cd) (RoHS)	max.5ppm
Mercury (Hg) (RoHS)	max.10ppm
Lead (Pb) (RoHS)	max.5ppm
Chromium (Cr) (RoHS)	max.10ppm
Brominated flame retardants (as Br) (RoHS)	max.1ppm