

# SPECIFICATION

## Tetrahydrofuran, Stabilizer Free

for RoHS

REQUIREMENT	SPECIFICATION
Appearance	Colorless clear liquid
Density (20°C)	0.884~0.889g/ml
Refractive index 20°C	1.406~1.409
Absorbance (250nm)	max.0.50
Absorbance (280nm)	max.0.20
Absorbance (350nm)	max.0.02
Water	max.0.1%
Peroxides (as H <sub>2</sub> O <sub>2</sub> )	max.0.005%
Assay (capillary GC)	min.99.5%
Cadmium (Cd) (RoHS)	max.10ppm
Mercury (Hg) (RoHS)	max.10ppm
Lead (Pb) (RoHS)	max.100ppm
Chromium (Cr) (RoHS)	max.10ppm
Brominated flame retardants (as Br) (RoHS)	max.1ppm