

SPECIFICATION

Toluene

for RoHS

REQUIREMENT	SPECIFICATION
Appearance	Colorless clear liquid
Assay (C ₆ H ₅ CH ₃) (GC)	min.99.5%(mass/mass)
Density (20°C)	0.864~0.868g/ml
Refractive index 20°C	1.496~1.498
Water	max.0.03%(mass/mass)
Residue after evaporation	max.0.001%(mass/mass)
Acidity (as HCl)	max.0.001%(mass/mass)
Alkalinity (as NaOH)	max.0.001%(mass/mass)
Sulfur compounds (as S)	max.0.003%(mass/mass)
Thiophene	to pass test
Substances darkened by sulfuric acid	to pass test
Cadmium (Cd) (RoHS)	max.10ppm
Mercury (Hg) (RoHS)	max.10ppm
Lead (Pb) (RoHS)	max.100ppm
Chromium (Cr) (RoHS)	max.10ppm
Brominated flame retardants (as Br) (RoHS)	max.1ppm