


OBNUC 1H  
 EXMOD NON  
 OBFRQ 399.65 MHz  
 OBSET 124.00 KHz  
 OBFIN 10500.0 Hz  
 POINT 32768  
 FREQU 8000.0 Hz  
 SCANS 8  
 ACQTM 4.096 sec  
 PD 2.904 sec  
 PW1 6.2 us  
 IRNUC 1H  
 CTEMP 25.7 c  
 SLVNT DMSO  
 EXREF 0.00 ppm  
 BF 0.12 Hz  
 RGAIN 14



品名
ポリスチレン