


1H
 NON
 399.65 MHz
 124.00 KHz
 10500.00 Hz
 32768
 7992.01 Hz
 8
 4.1001 sec
 2.9000 sec
 6.50 usec
 1H 24.2 c
 DMSO
 0.00 ppm
 0.24 Hz
 20

OBNUC
 EXMOD
 OBFRQ
 OBSET
 OBFIN
 POINT
 FREQU
 SCANS
 ACQTM
 PD
 PW1
 IRNUC
 CTEMP
 SLYNT
 EXREF
 BF
 RGAIN



品名
フルジオキシニル