


OBNUC 1H
 EXMOD NON
 OBFRQ 399.65 MHz
 OBSET 124.00 KHz
 OBFIN 10500.00 Hz
 POINT 32768
 FREQU 7992.01 Hz
 SCANS 8
 ACQTM 4.1001 sec
 PD 4.9500 sec
 PW1 6.70 usec
 IRNUC 1H
 CTEMP 24.3 c
 SLVNT CDCL3
 EXREF 0.00 ppm
 BF 0.12 Hz
 RGAIN 15



品名
イプロゾン