


OBNUC 1H
EXMOD NON
OBERQ 399.65 MHz
OBSET 124.00 KHz
OBFIN 10500.00 Hz
POINT 32768
FREQU 7992.01 Hz
SCANS 8
ACQTM 4.1001 sec
PD 4.9500 sec
PW1 6.70 usec
IRNUC 1H
GTEMP 24.5 c
SLVNT CDCL3
EXREF 0.00 ppm
BF 0.12 Hz
RGAIN 16



品名
チオアセトヒドロキシサム酸メチル