


OBNUC 1H  
EXMOD NON  
OBFRQ 399.65 MHz  
OBSET 124.00 KHz  
OBFIN 10500.00 Hz  
POINT 16384  
FREQU 7992.01 Hz  
SCANS 8  
ACQTM 2.0500 sec  
PD 4.9500 sec  
PWI 6.50 usec  
IRNUC 1H  
CTEMP 27.3 c  
SLVNT CDCL3  
EXREF 0.00 ppm  
BF 0.12 Hz  
RGAIN 17



品 名
3-ヒドロキシカルボフラン