


1H NON
 398.05 MHz
 124.00 KHz
 10500.00 Hz
 32768
 7992.01 Hz
 8
 4.1001 sec
 4.9500 sec
 6.70 usec
 1H 24.5 c
 DMSO
 4.65 ppm
 0.12 Hz
 16

OBNUC
 EXMOD
 OBFRQ
 OBSET
 OBFIN
 POINT
 FREQU
 SCANS
 ACQTM
 PD
 PW1
 IRNUC
 CTEMP
 SLYNT
 EXREF
 BF
 RGAIN



品名
アチレン