


1H
 NON
 399.05 MHz
 124.00 KHz
 10500.00 Hz
 32768
 7992.01 Hz
 8
 4.1001 sec
 2.9000 sec
 6.50 usec
 1H
 6348.8 c
 CDCL3
 0.00 ppm
 0.12 Hz
 21

OBNUC
 EXMOD
 OBFRQ
 OBSET
 OBFIN
 POINT
 FREQU
 SCANS
 ACQTM
 PD
 PW1
 IRNUC
 CTEMP
 SLVNT
 EXREF
 BF
 RGAIN



品名
メチルアセト