


IH
 OBNUC
 EXMOLD
 OBN78Q
 OBN8T
 OBNFN
 POINT
 FREQU
 SCANS
 ACQTM
 PD
 FV1
 IH
 OBNUC
 CTRDP
 SELVT
 EXCOR
 RF
 RGAIN
 392.78 MHz
 4.15 KHz
 7.29 Hz
 16384
 7883.00 Hz
 8
 2.137 sec
 5.000 sec
 5.00 msec
 24.2 e
 DMSO
 0.00 ppm
 0.12 Hz
 40



品名
ポリマー