


1H  
 NON  
 399.65 MHz  
 124.00 KHz  
 10500.00 Hz  
 32768  
 7992.01 Hz  
 8  
 4.1001 sec  
 2.9000 sec  
 6.50 usec  
 1H  
 24.7 °C  
 DMSO  
 0.00 ppm  
 2.12 Hz  
 19  
 OBNUC  
 EXMOD  
 OBFRQ  
 OBSET  
 OBFIN  
 POINT  
 FREQU  
 SCANS  
 ACQTM  
 PD  
 PW1  
 IRNUC  
 CTEMP  
 SLVNT  
 EXREF  
 BF  
 RGAIN



|            |
|------------|
| 品名         |
| クロキンセツメキシル |