


ORNIC 1H
EXMOD proton.jpg
ORFNO 399.78 MHz
ORSET 4.19 kHz
ORFIN 7.29 Hz
POINT 16384
FREQU 7603.00 Hz
SCANS 8
ACQTH 2.1837 sec
PD 5.0000 sec
PWI 4.95 usec
ORNIC 1H
CTEMP 23.8 c
SOLVT CDSCN
ROROP 1.93 ppm
RF 0.12 Hz
RGAIN 50



品名
ポリメチルアクリレート