


1H  
 NON  
 399.65 MHz  
 124.00 KHz  
 10500.00 Hz  
 32768  
 7992.01 Hz  
 8  
 4.1001 sec  
 2.9000 sec  
 6.90 usec  
 1H  
 DMSO  
 26.6 °  
 2.49 ppm  
 0.12 Hz  
 24

OBNJC  
 EXMOD  
 OBFRQ  
 OBSET  
 OBFIN  
 POINT  
 FREQU  
 SCANS  
 ACQTM  
 PD  
 PW1  
 IRNJC  
 CTEMP  
 SLVNT  
 EXREF  
 BF  
 RGAIN



品名
オキシカルボキシ