

## SPECIFICATION

Acetic Acid  
for LC/MS

REQUIREMENT	SPECIFICATION
Appearance	Colorless clear liquid
Solubility in water	to pass test
Absorbance (1→4, 250nm)	max.0.50
Absorbance (1→4, 254nm)	max.0.10
Absorbance (1→4, 260nm)	max.0.02
Absorbance (1→4, 270nm)	max.0.005
Absorbance (1→4, 300~400nm)	max.0.003
Water	max.0.3%
Fluorescence test	to pass test
Suitability for LC/MS analysis	to pass test
Assay (HPLC)	min.99.5%